

LENS MATERIALS

InstaShades® PolyClear® Gray and Brown

Diameter / Decentration	74mm / 3.0mm
Base Curves	1.25, 3.25, 5.50, 7.50
Rx Range	-8.50 to +5.00
Add Powers	+1.00 to +3.00

InstaShades Gray and Brown, 1.56 and 1.6 EvoClear®

Diameter / Decentration	72mm, 76mm / 3.0mm
Base Curves	0.50, 1.25, 3.25, 5.50, 7.50
Rx Range	-10.00 to +6.00
Add Powers	+1.00 to +3.00

Corning® SunSensors® Gray and Brown, 1.56

Diameter / Decentration	74mm / 3.0mm
Base Curves	0.50, 1.25, 3.25, 5.50, 7.50
Rx Range	-10.00 to +5.00
Add Powers	+1.00 to +3.00

1.67 High Index

Diameter / Decentration	75mm / 3.0mm
Base Curves	0.75, 2.50, 4.50, 6.50
Rx Range	-10.00 to +5.50
Add Powers	+1.00 to +3.00

TLX1.6™

Diameter / Decentration	74mm / 3.0mm
Base Curves	0.50, 1.25, 3.25, 5.50, 7.50
Rx Range	-10.00 to +5.00
Add Powers	+1.00 to +3.00

1.6 and 1.56 EvoClear

Diameter / Decentration	74mm / 3.0mm
Base Curves	0.50, 1.25, 3.25, 5.50, 7.50
Rx Range	-10.00 to +5.00
Add Powers	+1.00 to +3.00

PolyClear

Diameter / Decentration	78mm / 3.0mm
Base Curves	1.25, 3.25, 5.50, 7.50
Rx Range	-8.50 to +5.00
Add Powers	+1.00 to +3.00

Trivex™

Diameter / Decentration	75mm / 3.0mm
Base Curves	1.25, 3.25, 5.50, 7.50
Rx Range	-8.50 to +5.00
Add Powers	+1.00 to +3.00

Standard Resin and Standard Resin with Scratch Resistance

Diameter / Decentration	74mm / 3.0mm
Base Curves	1.25, 3.25, 5.50, 7.50
Rx Range	-8.50 to +5.00
Add Powers	+1.00 to +3.00