



KODAK Precise Lens

KODAK Precise Short Lens

KODAK Progressive Lenses are an excellent choice for everyday wear. Clear viewing areas work together for a natural-feeling wearing experience while maintaining great individual performance.

Outstanding Design

KODAK Precise® Lens is the first progressive design created with Signet Armorlite's proprietary Vision First Design™ Technology. This technology reverses the traditional design methodology of calculating the lens surface and measuring results. Instead, designers start by defining the optical properties that constitute superb vision and let those calculations determine the corresponding lens surface. This approach gives direct control of the curvature of the lens.

Premium Performance

The result, continuous power progression across the entire lens and smooth transition between viewing areas for easier patient adaptation. Plus, the perfectly placed reading, intermediate and

distance areas on the lens reduce swim effects. In fact, some wearers have compared their first KODAK Precise Progressive Lens experience to that of a single vision lens.

The additional binocular characteristics found in KODAK Precise Lens improve the visual balance of peripheral vision in both eyes. Wearers enjoy enhanced peripheral line integrity without experiencing a momentary blurry sensation.

For smaller frames, KODAK Precise Short Lens offers the same technology and award-winning design in a short corridor with a minimum 13mm fitting height.

Great Selection

KODAK Progressive Lenses are available in a variety of lens materials, including:

- Signia™ clear lens materials with the durable hard coat ArmorCoat™; compatible with all major anti-reflective coatings
- Transitions® Signature® Gen 8 and PhotoViews™ photochromics
- Polarized



KODAK Lens

KODAK Concise Lens

Great Option

KODAK Concise® Lenses aren't far behind when it comes to providing smooth viewing. This short-corridor lens design provides a spacious clear distance area, wide corridor and large reading area for fashion frames. Fitting heights range between 14mm and 17mm.

No matter which KODAK Progressive Lens you choose, your patients will enjoy the confidence of a trusted brand, great optics and appealing eyewear.

Availability

DESIGN	LENS MATERIAL/INDEX	DIAMETER	BASE CURVES	RX RANGE
KODAK Precise Lens	1.50 (coated and uncoated)	74/78mm	1.50, 3.25, 5.00, 7.00, 8.50	-9.00 to +6.00
	Poly	78mm	1.50, 3.25, 5.00, 7.00	-10.00 to +5.00
	Trivex®	75/80mm	1.50, 3.25, 5.00, 7.00	-10.00 to +4.50
	1.60 (coated and uncoated)	73/78mm	1.50, 3.25, 5.00, 7.00, 8.50	-11.75 to +7.25
	1.67 (coated and uncoated)	73/78mm	1.50, 3.25, 5.00, 7.00, 8.50	-13.00 to +8.00
	Polarized 1.50 (g/b)	81mm	3.25, 5.00, 7.00	-7.00 to +5.00
	Transitions Gen 8 1.50 (g)	76mm	1.50, 3.25, 5.00, 7.00	-9.00 to +6.00
	Transitions Gen 8 Poly (g)	78mm	1.50, 3.25, 5.00, 7.00	-10.00 to +5.00
	Transitions Gen 8 1.67 (g)	73/78mm	1.50, 3.25, 5.00, 7.00, 8.50	-13.00 to +8.00
	PhotoViews 1.50 (g/b)	76mm	1.50, 3.25, 5.00, 7.00	-9.00 to +6.00
	PhotoViews Poly (g/b)	78mm	1.50, 3.25, 5.00, 7.00	-10.00 to +5.00
KODAK Precise Short Lens	1.50 (coated and uncoated)	74mm	2.00, 4.50, 5.50, 7.50	-8.50 to +5.25
	Poly	78mm	2.00, 4.50, 5.50, 7.50	-10.00 to +6.00
	1.67 (coated and uncoated)	78mm	1.00, 2.00, 4.50, 5.50, 7.50	-12.50 to +7.00
	Transitions Gen 8 1.50 (g)	76mm	2.00, 4.50, 5.50, 7.50	-8.50 to +5.25
	Transitions Gen 8 Poly (g)	78mm	2.00, 4.50, 5.50, 7.50	-10.00 to +6.00
	PhotoViews 1.50 (g/b)	76mm	2.00, 4.50, 5.50, 7.50	-8.00 to +5.00
	PhotoViews Poly (g/b)	78mm	2.00, 4.50, 5.50, 7.50	-10.00 to +6.00
KODAK Concise Lens	1.50 (coated and uncoated)	74mm	1.25, 3.25, 5.50, 7.50	-9.00 to +5.00
	Poly	78mm	1.25, 3.25, 5.50, 7.50	-11.00 to -6.00
	Trivex	75mm	1.25, 3.25, 5.50, 7.50	-8.50 to +5.00
	1.60 (coated and uncoated)	78mm	.50, 1.25, 3.25, 5.50, 7.50	-11.75 to +6.25
	1.67 (coated and uncoated)	78mm	.75, 2.50, 4.50, 6.50	-13.00 to +4.50

g = gray
b = brown

KODAK Lens
See the Colors of Life®

Signet Armorlite, Inc.
800.759.4630
www.signetarmorlite.com

